



Lindy Phono to TosLink (Optical) and Coaxial ADC



Model: 70309

Manufacturer: LINDY

EAN: 4002888703093

Product Code: 627670

R1,514

ADCs and DACs allow for simple connectivity of digital or analogue audio equipment to modern, or legacy audio inputs.

The Lindy Phono to TosLink (Optical) and Coaxial ADC allows the user to easily convert analogue stereo audio signals to digital coaxial and Toslink (optical) output signals, for a high quality audio experience with movies, games and music.

With L/R Input connections, and both Optical and Digital Coaxial output ports, that can be connected individually or consecutively to ensure seamless compatibility, this audio converter is a perfect solution for connecting DVD Players, VCRs and older generation games consoles to home theatre receivers or soundbars. This device ensures there is no loss in quality for a superior surround-sound audio experience that enhances the impact of video or audio content. The separate dual output connectors can also work as a splitter to two separate audio receivers.

The product information provided is for reference purposes only. Technical specifications, photos, descriptions and prices may change without prior notice. The manufacturer and seller are not responsible for possible data discrepancies or typographical errors. We recommend checking the current information before purchasing.

itworkup.co.za | sales@itworkup.co.za | +27 (11)541-9950

The converters compact design ensures the device can be integrated into current installations or hidden away, while the digital connection switch to determine which input is active ensures fuss-free connectivity and use.

The product information provided is for reference purposes only. Technical specifications, photos, descriptions and prices may change without prior notice. The manufacturer and seller are not responsible for possible data discrepancies or typographical errors. We recommend checking the current information before purchasing.

itworkup.co.za | sales@itworkup.co.za | +27 (11)541-9950